

eDART Dual External Dart Valve

The external dual eDART valve is optimised for fine control of slurry flow specifically designed with the flotation market in mind. There are a number of body and flange orientations offered as standard but any customisation may be designed.

Material of Construction

- Plug and seat polyurethane or other appropriate wear resistant material (e.g. UHMWPE).
- Patented bellows seal. non-sliding sealing arrangement
- Body rubber lined mild steel
- eDART actuators

Standard Sizes

• 100mm to 1000mm

Options

- eDART dual valve controller
- eDART Thief sampler
- Flushing valves
- Full bore or reduced plug and seat
- Custom designs available if standard designs don't suit application.
- Smart (HART, Profibus), Electro-Pneumatic (4-20mA), Pneumatic (20-100kPa) Positioner
- Bias Spring Fail Closed, Fail Fixed or Double Acting Actuator Options

Features

- Body fully customised to Plant Layout
- front left/right; side or vertical outlet
- Cage guided plugs
- Inspection/thief sampler port
- Valve can be fully serviced in situ
- Simple maintenance: All internal wearing parts can be inspected and/or replaced without removing the valve body from the process line
- Anti Rotation Device
- Stroke Indication

Applications

Flotation machine level control

Distribution box level control





eDART Dual External Dart Valve


Outlet Pipe diameter for the dual edart

The following table gives the final flow diameter for the dual edart valve (units in mm):

Seat	Outlet Diameter	Pipe (6mm thickness)		Rubber Lining	
Diameter		OD	ID	Thickness	ID
80	150	165.2	153.2	4	145.2
100	200	219.1	207.1	4	199.1
150	250	273	261	4	253
200	350	355.6	343.6	6	331.6
250	400	406.4	394.4	6	382.4
300	500	508	496	6	484
400	600	609.6	597.6	6	585.6

Valve Coefficient (Cv) for the dual edart

The valves are named with an XY designation where X refers to the primary and Y to the secondary seat. A means that the seat is full size and B means there is a size reduction. This means that a 200AB valve has a primary seat of 200mm and secondary seat of 150mm. The calculated Cv is shown in the table below:



Email: sales@dualvalves.com.au